

SOFTSEAL[®] FILTER MASK+

PARTICULATE FILTRATION
plus CoolTech™ Valve

BETTER FIT for BETTER PROTECTION
and INCREASED COMFORT

UNIQUE PATENTED DESIGN
Seals NOSE, CHIN,
AND CHEEKS with
medical-grade silicone



**360 DEGREE SILICONE SEAL
MOLDS TO FACE**
Covers nose,
chin, and cheeks

**PARTICULATE
FILTER**
Filters $\geq 99\%$
of bacteria and
particles < 0.1
micron

**CRUSH PROOF
INTERNAL SKELETON**
Prevents mask collapse
while breathing

**COOLTECH™
VALVE**
Reduces
heat and
humidity

**ADJUSTABLE
TENSIONING**
For better fit

**4-POINT ATTACHMENT
HEAD STRAP**
Ultrasonically welded
without staple holes
that leak

**COARSE
PARTICULATE
FILTER**

**FLAME & FLUID
PENETRATION
RESISTANT**



- CoolTech™ Valve keeps you cool and reduces moisture
- Stays sealed while you work, breathe, and speak
- Ideal for general construction work. Protects against mold spores, fiberglass, drywall and sanding dust
- Protection against non-harmful common household dusts, dirt, pollen, grass and garden clippings

SOFTSEAL[®]
The Difference is the Seal

SOFTSEAL[®] FILTER MASK+

PARTICULATE FILTRATION
plus CoolTech™ Valve



UNIQUE PATENTED DESIGN
Seals NOSE, CHIN,
AND CHEEKS with
medical-grade silicone



**FLEXIBLE
SILICONE SEAL**
Gives you 360 degrees
of protection



Why other dust masks may fail to protect you

If your dust mask doesn't seal to your face and remain sealed, the simple fact is you are NOT protected. Most dust masks don't even pretend to seal.

Particles in and around your nose after wearing a mask indicates the seal around the edges of the mask has failed, allowing particles into your breathing zone. The facial seal is the single most important factor in protecting your lungs.

What makes SoftSeal masks better

SoftSeal masks are specifically designed to seal to your face, remain sealed so you stay protected, and be comfortable to wear for extended periods. Here's how:

SILICONE SEAL

- The 360 degree silicone seal molds to your face, maintaining the seal even while speaking or moving.
- As you inhale, the thin, feathered edge of the silicone seal tightens to your face.
- Molded-in adjustable nose clip can be shaped to your nose and won't peel off.

PERSONALIZED FIT FOR A TIGHT SEAL

- Four sizes ensure a personalized fit and tight seal.
- While most masks use staples that can leak, SoftSeal's 4-point, wide head straps are molded into the silicone face seal to help prevent leakage.
- Dual straps above and below the ears provide sealing forces in two directions.
- Tensioning clips in each head strap enable manual adjustment for an even better fit.

COMFORT

- No itchy material against your skin.
- An internal skeleton prevents mask collapse while breathing and improves the mask's durability.
- SoftSeal's no-fog design keeps goggles and glasses fog-free.
- The CoolTech™ exhalation valve keeps you cool and reduces moisture.



Available in 4 sizes for a personalized fit:

- Small (fits children)
- Medium
- Large
- X-Large

Also
available
in a VFold
style —
low profile
& foldable



Distributed by:

DDME, Inc.
800.513.9337
www.softsealmask.com

SOFTSEAL[®]
The Difference is the Seal