

TECHNICAL DATA

Grab Bars

Decorative Grab Bars



MATERIALS: Grab bar is constructed using 1-1/4" diameter 20 gauge 304 stainless steel tubing. Decorative posts and trim rings are cast in zinc. Trim rings are held in place using a friction fit. Meets ADA and ANSI A117.1-2003 for form and load bearing requirements.

INSTALLATION: Install grab bar with 3 - #10 x 2-1/2" flat head stainless steel screws provided for each end wall flange. Slide cover flanges over wall flanges and press firmly to complete installation.

OPTIONAL FASTENER INFORMATION: Wall studs or Wood blocking is preferable behind all wall surfaces. If wood blocking is not available, the following fasteners are suggested: Non-Stud Wall anchor.

SPECIFICATION: Surface mounted assist bar shall be model _____ (fill in model number) by Liberty Hardware Manufacturing Corporation.

Collection	A (Total Length)	B (Height)	C (Post Base Diameter)
Alexandria	20-7/8" (531.2mm)	3" (76 mm)	2-7/8" (74 mm)
Crestfield	20-7/8" (531.2mm)	3" (76 mm)	2-7/8" (74 mm)
Greenwich	20-7/8" (531.2mm)	3" (76 mm)	2-7/8" (74 mm)
Jamestown	20-7/8" (531.2mm)	3" (76 mm)	2-7/8" (74 mm)
Providence	20-7/8" (531.2mm)	3" (76 mm)	2-7/8" (74 mm)
Silverton	21-3/8" (544mm)	3-1/8" (80 mm)	3-3/8" (86.8 mm)
Celise	21" (533.2mm)	2-7/8" (73 mm)	3" (76 mm)
Elegance	20-7/8" (531.2mm)	3" (76 mm)	2-7/8" (74 mm)
Windemere	20-7/8" (531.2mm)	2-15/16" (75 mm)	2-7/8" (74 mm)

